



Flexible Conduit D40



Flexible Conduit D40 offers a secure and flexible means of laying cables and hoses. The integrated hook-and-loop fastening is used to turn this neoprene material into a tube that can be adapted precisely to fit the cables it carries and the route it needs to follow. The maximum internal diameter is 40 mm.

Neoprene cellular rubber (CR) is highly resistant to heat, oil, acids and bases and exhibits low flammability.

Scope of Delivery

Technical note

[0.0.719.00](#) For more information, please click here!

Properties	
Article number	0.0.719.00
Delivery unit	1 roll, length 3 m
Weight	281.0 g

Accessoires