



Profile 8 40x40, natural



Profile 8 40x40 is a universal construction profile made of high-quality anodized aluminium in the modular dimension of Line 8. This robust aluminium profile in the standard design variant from item features four open Line 8 profile grooves.



Scope of Delivery

Technical note

[0.0.026.03](#) Please click here for further information!

Properties	
Article number	0.0.026.03
Colour	natural
Delivery unit	cut-off max. 6000 mm
Weight	2.47 kg/m
Material	Al, anodized
Cross-sectional area	9.16 cm ²
Moment of Inertia, torsional	1.88 cm ⁴
Moment of Inertia, x-axis	13.96 cm ⁴
Moment of Inertia, y-axis	13.96 cm ⁴
Resistance Moment, x-axis	6.98 cm ³
Resistance Moment, y-axis	6.98 cm ³
Permissible groove extraction force	5000 N

Accessoires	
0.0.427.09	Cap 8 40x40 Zn, black
0.0.627.16	Cap 8 40x40, grey similar to RAL 7042
0.0.026.01	Cap 8 40x40, black