



Profile 8 40x40 E, natural



Profile 8 40x40 E is a universal construction profile made of high-quality anodized aluminium in the modular dimension of Line 8. This considerably weight-reduced aluminium profile in the E (economy) design variant from item features four open Line 8 profile grooves.



Scope of Delivery

Technical note

[7.0.000.09](#) Please click here for further information!

Properties	
Article number	7.0.000.09
Colour	natural
Delivery unit	cut-off max. 6000 mm
Weight	1.37 kg/m
Material	Al, anodized
Cross-sectional area	5.07 cm ²
Moment of Inertia, torsional	1.09 cm ⁴
Moment of Inertia, x-axis	7.38 cm ⁴
Moment of Inertia, y-axis	7.38 cm ⁴
Resistance Moment, x-axis	3.69 cm ³
Resistance Moment, y-axis	3.69 cm ³
Permissible groove extraction force	1750 N

Accessoires	
0.0.026.01	Cap 8 40x40, black
0.0.627.16	Cap 8 40x40, grey similar to RAL 7042
0.0.427.09	Cap 8 40x40 Zn, black